


# LSL-EFA 2

## LIFT SYSTEM LIGHT WITH ELECTRIC FLAP



future automation





| SPECIFICATION                    | MEASUREMENTS   |
|----------------------------------|--|
| Screen Sizes (Approx)            | 32" - 40"  |
| Maximum Weight Capacity          | 25Kg (55lb)  |
| Maximum Weight Capacity (Marine) | 16Kg (35lb)  |
| Maximum Screen Height            | 524mm (20.6")  |
| Packaging Dimensions             | 920mm (36.2") x 550mm (21.7") x 250mm (9.8")   |
| Shipping Weight                  | 18Kg (40lb)  |
| Movement Type                    | Motorised  |
| Power Supply Required            | 110V or 240V AC  |
| Power Consumption                | 250-500W   |
| Power Consumption Standby        | 3W   |
| Decibel Rating                   | 58dB   |
| Mounting Patterns Supported      | VESA 200 W x 300, 200 H  |
| Control Options                  | IR Remote, RS232, Contact Closure  |
| Product Options / Features       | Specific B&O and Loewe mounts / adapters, Custom RAL paint finishes, Outdoor version |
| Package Contents                 | Mechanism, IR remote control   |
| Marine Suitable                  | Yes (Indoor)   |


### CABLE ROUTING

Screen cables are routed behind the Base Panel and out the right side of the Beam into the Cable Track. Cables must be routed carefully to prevent any interference with the LSL beam as it operates.


Screen and Mechanism cables should be routed to a control box in the bottom of the cabinet.



### MECHANISM UP - IN CABINET



### MECHANISM DOWN - IN CABINET



SECTION D-D


### TECHNICAL SHEET

ISSUE 005

SHEET 5

## LIFT SYSTEM LIGHT WITH ELECTRIC FLAP


### BASE PANEL & FLAP PANEL DETAILS



### POSITIONING THE EFA TO ACCOMADATE SMALLER SCREENS




A Base Panel of less than 1050mm [41.3] wide will cause the EFA to interfere with the LSL beam.

This can be avoided by orientating the EFA away from the LSL. It will however require more space for the EFA to be positioned to the side of the cabinet.



### OVERALL MECHANISM DIMENSIONS

#### MECHANISM UP



#### MECHANISM DOWN

